



HOW TO CONFIGURE YOUR MULTI-DISPLAY CEILING MOUNT:

Follow These 3 Simple Steps to Choose Your Options

1

CHOOSE THE MULTI-DISPLAY CEILING MOUNT TO USE:



DST965

Back-to-Back Ceiling Mount
for 40"-65" Displays



DST970X2

Dual-Display Ceiling Mount
for 40"-70" Displays



DST980-3

Multi-Display Ceiling Mount
with 3 Telescoping Arms
for 37"-80" Displays



DST975-4

Multi-Display Ceiling Mount
with 4 Telescoping Arms
for 37"-75" Displays



DST942-6

Multi-Display Ceiling Mount
with 6 Telescoping Arms
for 37"-42" Displays

2

CHOOSE THE EXTENSION COLUMN TO USE (must start with "ADD"):

- ADD018024:** Adjusts 18"-24" in 2" increments
ADD0203: Adjusts 24"-36" in 2" increments
ADD0305: Adjusts 36"-60" in 2" increments
ADD0406: Adjusts 48"-72" in 2" increments
ADD0507: Adjusts 60"-84" in 2" increments
ADD0608: Adjusts 72"-96" in 2" increments
ADD0709: Adjusts 84"-108" in 2" increments
ADD0810: Adjusts 96"-120" in 2" increments
ADD0911: Adjusts 108"-132" in 2" increments
ADD1012: Adjusts 120"-144" in 2" increments



3

CHOOSE THE CEILING ADAPTOR TO USE:



DCT300

Multi-Display
Truss Ceiling
Stress Decoupler



DCS400

Multi-Display
Structural Ceiling
Stress Decoupler



Multi-Display I-Beam Clamps

See below for complete part numbers

- DCT500:** Fits 7"-12" W, .25"-1" thick
DCT600: Fits 15"-19.5" W, 1.5"-2" thick
DCT800: Fits 7"-12" W, 2.5"-3" thick
DCT900: Fits 4"-7" H, up to 1.5" thick

Hours of Operation: Mon-Fri, 7 AM – 6 PM | info@peerless-AV.com | 630.375.5100 | peerless-AV.com

peerless-AV®

© 2024 Peerless Industries, Inc. All rights reserved.